



RE-BOX® – Commercial Equipment Cabinet

Pre-Configured Version

Contents: base/rear section with welded 19" brackets for 2 hubs, front door with 2 locks (NSQ tool), a set of 19" extension brackets for 3 additional hubs (RE4xx only) and a set 19" bottom hinge brackets for patch panels

Switch Capacity	Max. Switch Depth	Height	Width	Depth	Color	Catalog No.
2U	14" (356)	32" (813)	24.2" (615)	7" (178)	Light gray	RE2
2U	14" (356)	32" (813)	24.2" (615)	7" (178)	Black	RE2B
5U	14" (356)	32" (813)	24.2" (615)	10" (254)	Light gray	RE4
5U	14" (356)	32" (813)	24.2" (615)	10" (254)	Black	RE4B
5U	22" (559)	42" (1067)	24.2" (615)	10" (254)	Light gray	RE4X
5U	22" (559)	42" (1067)	24.2" (615)	10" (254)	Black	RE4XB

User-Configurable Version

Contents: 1 base/rear section and 1 front door with 2 locks (NSQ tool) (IDF24 has only 1 lock)

Rack Width Units	Height	Width	Depth	Color	Catalog No.
2U	24" (600)	24.2" (615)	10" (254)	Light Gray	IDF24
4U	32" (813)	24.2" (615)	10" (254)	Light Gray	IDF32
6U	42" (1067)	24.2" (615)	10" (254)	Light Gray	IDF42



RE4XB

RE-BOX® 10GbE Cable Entry Pre-Configured Version

Same as standard pre-configured RE-BOX® except top conduit knockouts replaced with adjustable, high cable capacity grommet plate.

Contents: base/rear section with welded 19" brackets for 2 hubs, front door with 2 locks (NSQ tool), a set of 19" extension brackets for 3 additional hubs (RE4xx only) and a set 19" bottom hinge brackets for patch panels

Switch Capacity	Height	Width	Depth	Color	Catalog No.
2U	32" (813)	24.2" (615)	7" (178)	Light Gray	RE210G
5U	32" (813)	24.2" (615)	10" (254)	Light Gray	RE410G



RE410G