



1. [] DENOTE MILLIMETERS
2. SET SCREW IS 18-8 STAINLESS STEEL
3. OPERATING TEMPERATURE
-40°F (-40°C) TO 250°F (121°C)
4. EXCELLENT CHEMICAL RESISTANCE TO THE FOLLOWING:
SULFURIC ACID, HYDROCHLORIC ACID, SODIUM HYDROXIDE, METHYL ETHYL KETON, ACETONE, 1,1,1 TRICHLOROETHANE, METHANOL, IPA, ASTM #3 OIL, SAE 20 OIL, ALCONOX, TOLUENE, MINERAL SPIRITS, GLACIAL ACETIC ACID, DIESEL FUEL, HEPTANE, CELLOSOLVE ACETATE, AMMONIA, TURPENTINE, KEROSENE, WATER, AND GASOLINE
5. FOR USE INDOOR AND OUTDOOR
6. MAX SWITCH HANDLE WIDTH: .295 (7.5)

										CAD FILENAME/LAYERS		100919AM_DC_C10905/01A			
										PANDUIT CORP. TINLEY PARK, ILLINOIS					
										MINIATURE CIRCUIT BREAKER LOCKOUT PSL-MCB CUSTOMER DRAWING					
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .1 (XXX) ± .015 (.XX) ± .03 ANGLES ± 5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
										DRAWN BY JHAC	MAT'L; RED 33% GLASS-FILLED NYLON		SCALE 1 : 1		
0	4/28/11	JHAC		DRAWING RELEASE	6374					DATE 04/28/11			DRAWING NO. C10905		DWG A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP		CHK'D			SIZE		