




PANDUIT PART NO.	WEIGHT lbs 10 (g) pcs
JP75CMB- ---	.855 (388)



NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PRODUCT COLOR.
2. HOOK MATERIAL: NYLON 6/6
ANGLE BRACKET MATERIAL: PRE-GALVANIZED STEEL,
RIVET MATERIAL: ALUMINUM
3. PRODUCT IS DESIGNED TO SUPPORT A MAXIMUM OF 3/4" (19.05) DIAMETER BUNDLE. MAXIMUM RECOMMENDED STATIC LOAD: 15 lbs.
4. PRODUCT INCORPORATES FEATURES ALLOWING USER TO RETAIN CABLE BUNDLES IN J-PRO J-HOOK WITH TAK-TY CABLE TIES UP TO 3/4" WIDE.
5. PRODUCT MARKINGS:
 cULus logo and statement:
 "SUITABLE FOR USE IN AIR HANDLING SPACES IN ACCORDANCE WITH SECTION 300-22 (C) & (D) OF THE NATIONAL ELECTRIC CODE."
 ULC logo and statement:
 "IN ACCORDANCE WITH CAN/ULC S-102.2-10 IN SINGLE UNITS OR PAIRS, 4 ft (1220mm) MIN. SPACING, FSR=0, SDC=35."

OO	10/29/2012	DBLA	GGC	KLN	INITIAL RELEASE	GAECN00219
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE				
J-PRO CEILING MOUNT J-HOOK (JP75CMB-___)				
CONTROL DRAWING				
ITEM REVISION NAME			121031AA/00 	
DATASET FILE NAME				
121031AA_DC_C11000/00A				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °			MATERIAL: SEE NOTE 2	
 THIRD ANGLE PROJECTION			DRAWING NUMBER: C11000	
DRAWN BY	DATE	CHK	SCALE	SIZE
DBLA	10/29/2012	KLN	NONE	SHT 1 OF 1
				A

D10100DA/12