


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART #	DESCRIPTION	WEIGHT*
CJR688TG**	8 POSITION, 8 WIRE UNIVERSAL MODULE, RIGHT ANGLE WHITE WIRE CAP IS CODED FOR T568A AND T568B WIRING SCHEMES	1.742 LB/100 PCS (790g/100PCS

*WEIGHT IS APPROXIMATE
**JACK COLOR SUFFIX





STRAIN RELIEF CLIP




- RIGHT ANGLE
WIRE CAP

NOTES :

1. TX6 UTP RIGHT ANGLE JACK MODULE
2. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
3. WIRE CAP TERMINATES CABLE TO THE RIGHT OR THE LEFT.
4. 100% PERFORMANCE TESTED TO CATEGORY 6 COMPONENT LIMITS.
5. INDIVIDUALLY SERIALIZED AFTER TESTING FOR TRACEABILITY.
6. TERMINATES 22-26AWG SOLID OR STRANDED UTP CABLE.
7. OPERATING TEMPERATURE: -10°C TO 60°C (-14°F TO 140°F).
8. STORAGE TEMPERATURE: -40°C TO 70°C (-40°F TO 158°F).
9. C(UL)US LISTED-FILE NUMBER E129886
10. UNIVERSAL DESIGN ACCEPTS SIX AND EIGHT POSITION PLUGS.
11. MATERIAL: HOUSING-ABS, WIRE CAP-POLYCARBONATE.
12. DIMENSIONS IN PARENTHESES ARE METRIC.



ACTUAL SIZE

PART NUMBER CJR688TG**		PRODUCT SPEC/PKG SPEC N/A	
I.I. NUMBER N/A		WORK INSTRUCTION N/A	
TITLE TX6 UTP RIGHT ANGLE JACK MODULE			
CUSTOMER DRAWING			
ITEM REVISION NAME 13M407AB/00			
DATASET FILE NAME 13M407AB_DC01874-156/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] $.x \pm .1 [2.54]$ $.xxx \pm .005 [.127]$ $.xx \pm .01 [.25]$ ANGLES $\pm 5^\circ$		MATERIAL: SEE NOTE 11	
		DRAWING NUMBER: 01874-156	
DRAWN BY BJN	DATE 5-15-13	CHK JAV	SCALE FULL SHT 1 OF 1
		SIZE A	