

2



1


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
CP48HDBL	6.15 LB/10 PCS 12788.0 g/10 PCS

NOTES:

- SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS WITH THIS WIRING SYSTEM
- THE HIGH DENSITY PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- PACKAGE CONTAINS:
 - 48 PORT STAMPING
 - 8 POSITION FACEPLATES (ASSEMBLED TO PANEL)
 - GROUNDING STRIPS (ASSEMBLED TO PANEL)
 - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - SCREW KIT (INCLUDES FOUR M6 SCREWS)
 - M6 GROUNDING SCREWS
 - #12-24 GROUNDING SCREWS
- DIMENSION IN [] ARE IN METRIC.



PART NUMBER	CP48HDBL	PRODUCT SPEC/PKG SPEC	N/A
I.T. NUMBER	N/A	WORK INSTRUCTION	N/A
TITLE			
MINI-COM 48 PORT HIGH DENSITY SHIELDED MODULAR PATCH PANEL			
CUSTOMER DRAWING			
ITEM REVISION NAME		PANDUIT TM	
11M249AQ/00.PRT			
DATASET FILE NAME			
11M249AQ_DC/00A.PRT			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		MATERIAL :	
.x ± .xxx ± .010 [.3]		STAMPING-18 GAUGE	
.xx ± .03 [.8]		STAINLESS STEEL	
ANGLES :		GROUNDING STRIP-	
		PHOS BRONZE	
		FACEPLATE-ABS	
		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		11M249AQ-02	
DRAWN BY	DATE	CHK	SCALE
BJN	11-26-12	JSP	NONE
SHT 1 OF 1			SIZE
			A

2

1