


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



GPST (FRONT VIEW)



GPST (SIDE VIEW)



GPSTB (BLADE)

PANDUIT PART NO.

WEIGHT:

GPST Tool


.3 lb./each
(135 g./each)

GPSTB Blade

.03 lb./each
(12 g./each)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. PARTS INCLUDED ARE:
GPST SINGLE PUNCHDOWN TOOL
GPSTB SINGLE REPLACEMENT BLADE
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.
5. TERMINATES CABLE ON ALL GIGA-PUNCH™ TYPE PRODUCTS. REVERSIBLE BIT PROVIDES OPTION OF TERMINATING WITHOUT CUTTING WIRE.

							GPST / GPSTB CUSTOMER DRAWING					
							CUSTOMER DRAWING					
							ITEM REVISION NAME:					
							CG24580A01_01					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:			MATERIAL:		
							(.x) ± --- (.xxx) ± ---			HANDLE:		
							(.xx) ± --- ANGLES ± ---			PLASTIC/STEEL		
01	4-15-14	BLR	BJPU	ABJ	REDRAWN: NEW TEMPLATE	4737				BLADE: STEEL		
							THIRD ANGLE PROJECTION			DRAWING NUMBER: CG24580A01		
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY: BLR	DATE: 4-15-14	CHK BJPU	SCALE NONE	SHT 1 OF 1	SIZE A