




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES :

1. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUGS AT BOTH ENDS PER T568B.
2. CONSTRUCTED WITH 26AWG STRANDED CAT6A TWISTED PAIR LSZH/CM F/UTP PATCH CABLE.
3. NOMINAL CABLE JACKET DIAMETER IS 0.252 IN (6.3MM).
4. MATERIALS:
  - PLUG: POLYCARBONATE
  - PLUG SHIELD: PLATED CARTRIDGE BRASS
  - CABLE SHIELD: ALUMINUM
  - BOOT: TPE
5. STANDARD LENGTHS: 0.2M  
0.5M-9.5M (IN 0.5M INCREMENTS)  
10M-20M (IN 1M INCREMENTS)  
25M-50M (IN 5M INCREMENTS)

CABLE COLORS	** = COLOR
INTERNATIONAL GRAY	IG
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
WHITE	--
GRAY	GY

PART NUMBER		STP6Cxx***			
TITLE					
TX6A 10GIG F/UTP SHIELDED PATCH CORDS (CM/LSZH)					
CUSTOMER DRAWING					
ITEM REVISION NAME		14M504BC/00			
DATASET FILE NAME		14M504BC_DC02/00A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [ mm ]  .X ± .XXX ± .010 [ .3 ] .XX ± .03 [ .8 ]      ANGLES ±				MATERIAL :  SEE NOTES 2 & 4	
 THIRD ANGLE PROJECTION				DRAWING NUMBER: 1 4M504BC - 02	
DRAWN BY	DATE	CHK	SCALE	SIZE	
BJN	10-21-14	SCAL	NONE	SHT 1 OF 1	
				A	

R	10-21-14	BJN	SCAL	LPH	RELEASED TO PRODUCTION	14M504BC-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN