



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICMPPT24BLY	.52 LB/EACH PC (237.4 g/EACH PC)

NOTES:

- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- PART INCLUDES:
 - METAL STAMPING
 - 4 POSITION FACEPLATE WITH 2 LABEL POCKETS (ASSEMBLED TO METAL STAMPING)
 - CLEAR LABEL COVERS
 - SCREW KIT (INCLUDES FOUR #12-24 SCREWS)
 - SCREW KIT (INCLUDES FOUR M6 SCREWS)
- LABELS SOLD SEPARATELY.



PART NUMBER		UICMPPT24BLY	
TITLE		MINI-COM ULTIMATE ID 24 PORT MODULAR PATCH PANEL WITH 2 LABEL POCKETS PER FACEPLATE	
ITEM REVISION NAME		CUSTOMER DRAWING	
DATASET FILE NAME		M01207AJ-00	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT MATERIAL: STAMPING: C.R.S. FACEPLATE: ABS	
.X ± .XX ± .03 (.8) .XXX ± .010 (.3) ANGLES ±			
DRAWING NUMBER:		01207-08	
DRAWN BY	DATE	CHK	SCALE
JSP	7-17-02	JAJP	
SHT 1 OF 1		A	

2	5-2-14	BJN	JSP	MMR	REVISED & REDRAWN PREVIOUS REVISIONS REMOVED FOR CLARITY	01207-08
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN