



- NOTES:
1. SEE SHEET 2 FOR PART NUMBERS.
 2. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
 3. A. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
B. PLENUM RATED CABLE ASSEMBLIES MEET NFPA 262.
 4. CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596 AND TELCORDIA GR-409-CORE.
 5. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 6. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.



						TITLE 12 AND 24 FIBER MPO TO MPO SMALL DIAMETER TRUNK CABLE WITH PULLING EYE						
						CUSTOMER DRAWING						
						ITEM REVISION NAME 12F187FY/00						
						DATASET FILE NAME 12F187FY_DC/00A						
						UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]						
						.X ± .XXX ± .010 [0.3]						
						.XX ± .03 [0.8] ANGES ±						
						THIRD ANGLE PROJECTION						
R	12-16-14	MC	JDK	EJH	RELEASED TO PRODUCTION	12F187FY-DC						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	DRAWING NUMBER: 12F187FY-DC	
							MC	12-16-14	JDK	NONE	SHT 1 OF 2	SIZE B



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

1	2	3	4	5	6	7	8	9	10	11	12	13	14	15
F			Y			5		5						

FIBER TYPE

9 - SINGLEMODE - OS1/OS2
X - 50/125um - OM3
Z - 50/125um - OM4

FIBER COUNT

T - 12 FIBER
U - 24 FIBER

JACKET FLAME RATING

L - LSZH RATED
P - PLENUM RATED (OFNP)

CONNECTOR TYPE

5 - MTP (FEMALE)
6 - MTP (MALE)
7 - PANMPO (FEMALE) NOT AVAILABLE IN SINGLEMODE
8 - PANMPO (MALE) NOT AVAILABLE IN SINGLEMODE

PERFORMANCE/POLARITY

A - METHOD A POLARITY/STANDARD IL
B - METHOD B POLARITY/STANDARD IL
X - METHOD A POLARITY/OPTIMIZED IL
Y - METHOD B POLARITY/OPTIMIZED IL

PULLING EYE

A - PULLING EYE ON ONE END
C - PULLING EYE ON BOTH ENDS
N - NO PULLING EYE (PULLING EYE NOT RECOMMENDED FOR ASSEMBLIES LESS THAN 20 METERS/65 FEET)

UNIT OF MEASURE

M - METERS
F - FEET

LENGTH

001 - 999

B

B



A

A

R	12-16-14	MC	JDK	EJH	REFER TO SHEET 1 FOR REVISION HISTORY	12F187FY-DC

TITLE
12 AND 24 FIBER MPO TO MPO SMALL DIAMETER TRUNK CABLE WITH PULLING EYE
CUSTOMER DRAWING

ITEM REVISION NAME
12F187FY/00

DATASET FILE NAME
12F187FY_DC/00A

UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]
.X ± .XXX ± .010 [0.3]
.XX ± .03 [0.8] ANGLES ±

THIRD ANGLE PROJECTION

MATERIAL:

DRAWING NUMBER:
12F187FY-DC

DRAWN BY: MC DATE: 12-16-14 CHK: JDK SCALE: NONE

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
-----	------	----	-----	-----	-------------	-----

SHT 2 OF 2	SIZE B
------------	--------

