





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



- NOTES:
1. SEE TABLE 1 FOR PART NUMBERS.
 2. CONNECTOR MEETS THE REQUIREMENTS OF TIA-568-C.3.
 3. MPO POLARITY COMPLIES WITH METHOD "A" PER TIA 568-C.0
 4. A. LSZH-RATED CABLE ASSEMBLIES MEET IEC-60332, IEC-60754 AND IEC-61034 REQUIREMENTS.
B. PLENUM RATED CABLE ASSEMBLIES MEET NFPA 262.
 5. CABLE MEETS THE MECHANICAL REQUIREMENTS OF ICEA-S-83-596 AND TELCORDIA GR-409-CORE.
 6. ALL MATERIALS AND COMPONENTS USED MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2011/65/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
 7. MAXIMUM STRENGTH OF THE PULLING EYE IS 20 lbs.



	PANDUIT PART NUMBER	FIBER TYPE	FIBER COUNT	JACKET TYPE	CABLE DIAMETER (mm)
MTP	FXTYL5E5EAAMLLL	50/125 OM3	12	LSZH	4.6
	FZTYL5E5EAAMLLL	50/125 OM4			
	FXUYL5E5EAAMLLL	50/125 OM3	24	LSZH	5.1
	FZUYL5E5EAAMLLL	50/125 OM4			
	FXTYP5E5EAAMLLL	50/125 OM3	12	PLENUM	4.5
	FZTYP5E5EAAMLLL	50/125 OM4			
PANMPO	FXUY7E7EAAMLLL	50/125 OM3	12	LSZH	4.6
	FZUY7E7EAAMLLL	50/125 OM4			
	FXTYP7E7EAAMLLL	50/125 OM3	24	LSZH	5.1
	FZUY7E7EAAMLLL	50/125 OM4			
	FXTYP7E7EAAMLLL	50/125 OM3	12	PLENUM	4.5
	FZUY7E7EAAMLLL	50/125 OM4			
	FXUY7E7EAAMLLL	50/125 OM3	24	PLENUM	5.4
	FZUY7E7EAAMLLL	50/125 OM4			

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
2	06-24-13	SAT	WMA/JDK		RELEASED TO PRODUCTION	12F178BG-DC

TITLE 12 & 24 FIBER MPO TO MPO SMALL DIAMETER TRUNK CABLE WITH PULLING EYE		PANDUIT
CUSTOMER DRAWING		
ITEM REVISION NAME 12F178BG/01	MATERIAL:	
DATASET FILE NAME 12F178BG_DC/01B	DRAWING NUMBER: 12F178BG-DC	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		
.X ± .xxx ± .010 [0.3]	ANGLES ±	
.XX ± .03 [0.8]	THIRD ANGLE PROJECTION	
DRAWN BY SAT	DATE 03-11-13	CHK WMA
SCALE NONE	SHT 1 OF 1	
SIZE B		