





PANDUIT PART NUMBER	WEIGHT
FRIV4524X4	3.94 LB/EACH (1787g/EACH)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. THE FIBERRUNNER 24x4 INSIDE VERTICAL 45° ANGLE FITTING IS DESIGNED WITH A MINIMUM 3" (76.2) BEND RADIUS TO PROTECT FIBER OPTIC CABLES.
3. THE FIBERRUNNER 24x4 INSIDE VERTICAL 45° ANGLE FITTING INCLUDES:
ONE (1) INSIDE VERTICAL 45° ANGLE BASE
ONE (1) INSIDE VERTICAL 45° ANGLE COVER
4. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D39701C0_DC/00 FRIV4524X4

CAD FILENAME/LAYERS		FRIV4524X4.pdf	
PANDUIT		CORP	
TINLEY PARK, ILLINOIS		FIBERRUNNER 24x4 INSIDE VERTICAL 45° ANGLE FITTING (FRIV4524X4)	
CUSTOMER DRAWING		UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± (.XX) ± .03 (.8) ANGLES ±	
UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		SCALE NONE	
DRAWN BY MSO		DATE 10-21-08	
DATE 10-21-08		ABS	
CHK'D SL		DRAWING NO. 39701-23	
		DWG SIZE A	

REV	DATE	BY	CHK	DESCRIPTION	ECN	-	R	CUST	SUP	GMBH
R	10-21-08	MSO	SL	RELEASED TO PRODUCTION	39701-23		RN	RN		