


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART#	DESCRIPTION	WEIGHT*
CJE5E88TG**	8 POSITION, 8 WIRE UNIVERSAL MODULE. RED WIRE CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.73 LB/100 PCS (785g/100 PCS)

*WEIGHT IS APPROXIMATE
**JACK COLOR SUFFIX



NOTES:

- JACK MODULE USES SEALANT(S) TO PROTECT CONTACTS FROM CORROSION AND CONTAMINATION.
- RED WIRE CAP DESIGNATES CATEGORY 5e PERFORMANCE.
- TO DESIGNATE A JACK COLOR, ADD A TWO LETTER COLOR SUFFIX. SEE CURRENT CATALOG FOR AVAILABLE PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- MATERIAL:
 MODULE HOUSING - PBT
 WIRE CAP - PC
 STRAIN RELIEF CLIP - PC
- ALL TX5e CAT5e 8 POSITION, 8 WIRE CONNECTOR MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.



MODEL FILENAME	M01874AA/00	SIZE A
DRAWING FILENAME	M02115AA_DC13/00B	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
I	6-4-10	BJN	KAA	B. UPDATED TITLE BLOCK A. UPDATED WEIGHT	02115-13		PBD		
R	6-04-09	MDJr	AGF	RELEASED TO PRODUCTION	02115-13		PBD		

TX5e CAT5e CORROSIVE RESISTANT JACK MODULE CUSTOMER DRAWING

PANDUIT
TINLEY PARK, IL 60487

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ±.010(.3)
 (.XX) ±.03(.8) ANGLES ±

I.I. NUMBER	
PRODUCT SPEC/ PKG SPEC	
ASSY METHOD/ TEST METHOD	
SCALE	FULL
PART NO.	CJE5E88TG**
DRAWING NO.	02115-13

DRAWN BY: MDJr
 DATE: 3-18-09
 CHECK'D: AGF