





PANDUIT PART#	DESCRIPTION	WEIGHT*
CJE688TG**	8 POSITION, 8 WIRE UNIVERSAL MODULE. WHITE WIRE CAP IS COLOR CODED FOR T568A AND T568B WIRING SCHEMES.	1.73 LB/100 PCS (785g/100 PCS)

*WEIGHT IS APPROXIMATE
**JACK COLOR SUFFIX

NOTES:

1. JACK MODULE USES SEALANT(S) TO PROTECT CONTACTS FROM CORROSION AND CONTAMINATION.
2. WHITE WIRE CAP DESIGNATES CATEGORY 6 PERFORMANCE.
3. TO DESIGNATE A JACK COLOR, ADD A TWO LETTER COLOR SUFFIX. SEE CURRENT CATALOG FOR AVAILABLE PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
4. MATERIAL:
MODULE HOUSING - PBT
WIRE CAP - PC
STRAIN RELIEF CLIP - PC
5. ALL TX6 CAT6 8 POSITION, 8 WIRE CONNECTOR MODULES ARE UNIVERSAL IN DESIGN. THEY ACCEPT SIX AND EIGHT POSITION MODULAR PLUGS WITHOUT DAMAGE.
6. DIMENSIONS IN PARENTHESES ARE IN METRIC.



MODEL FILENAME M02115AA/00		SIZE A
DRAWING FILENAME 10M168BB_DC02/00B		
TX6 PLUS CORROSIVE RESISTANT JACK MODULE CUSTOMER DRAWING		
 TINLEY PARK, IL 60487		I.I. NUMBER PRODUCT SPEC/ PKG SPEC
 THIRD ANGLE PROJECTION		ASSY METHOD/ TEST METHOD SCALE FULL
ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ±.010(.3) (.XX) ±.031(.8) ANGLES ±		PART NO. CJE688TG**
DRAWN BY BJN	REVIEW DRAWING NUMBERS	DRAWING NO. 10M168BB-02
DATE 2-23-10	MAT'L	
CHK'D KAA		

I	6-4-10	BJN	CAA	B. UPDATED TITLE BLOCK A. UPDATED WEIGHT	10M168BB-02		PBD		
R	2-23-10	BJN	CAA	RELEASED TO PRODUCTION	10M168BB-02		PBD		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	OTH

