


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	MIN. CABLE LENGTH
NK5EPC3**Y	3 FT.
NK5EPC5**Y	5 FT.
NK5EPC7**Y	7 FT.
NK5EPC10**Y	10 FT.
NK5EPC14**Y	14 FT.
NK5EPC20**Y	20 FT.
NK5EPC1M**Y	1 METER
NK5EPC2M**Y	2 METERS
NK5EPC3M**Y	3 METERS
NK5EPC4M**Y	4 METERS
NK5EPC5M**Y	5 METERS

- NOTES:
IDENTIFICATION:
**1. SEE CURRENT NETKEY CATALOG FOR PACKAGE QUANTITIES AND AVAILABLE COLORS.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. TERMINATED WITH (8-POSITION) MODULAR PLUGS ON BOTH ENDS PER T568A.
4. CONSTRUCTED WITH 4-PAIR/24 AWG STRANDED UTP CAT 5e NON-PLENUM PATCH CABLE.
5. MATERIAL:
PLUG: POLYCARBONATE

T568A WIRING SCHEME

PLUG POSITION	CABLE WIRE
1	WHITE GREEN
2	GREEN
3	WHITE ORANGE
4	BLUE
5	WHITE BLUE
6	ORANGE
7	WHITE BROWN
8	BROWN

PART NUMBER		SEE TABLE ABOVE	
TITLE			
NETKEY CATEGORY 5E PATCH CORD			
CUSTOMER DRAWING			
ITEM REVISION NAME		M02479LL/07	
DATASET FILE NAME		M02479LL_DC299/07A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)		MATERIAL:	
.x ± .xxx ± .010 (.3)		SEE NOTE 5	
.xx ± .03 (.8) ANGLES ±		DRAWING NUMBER:	
THIRD ANGLE PROJECTION		02479-299	
DRAWN BY	DATE	CHK	SCALE
NER	3-21-06	WJC	NONE
SHT 1 OF 1		A	

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
3	5-13-14	MDJR	REFR	JCK	ALL PREVIOUS REVISIONS OMITTED FOR CLARITY. A. UPDATED TITLE BLOCK.	02479-299

D10100DA/14