


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT
PART NO.

WEIGHT
(APPROX.)

NK5EPPG24Y

1.25 lb (567 g)

NOTES:

- MATERIAL:
PANEL HOUSING: STEEL
RJ45 MODULE: THERMOPLASTIC RESIN UL94V-0
PUNCHDOWN BLOCKS: THERMOPLASTIC RESIN UL94V-0
BEZEL ASSEMBLY: THERMOPLASTIC RESIN UL94H-B
RETENTION CAP: THERMOPLASTIC RESIN UL94V-0
- 24 PORT PATCH PANEL 8 POSITION 8 WIRE.
- THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- FOUR (4) 12-24 X 1/2" ROUND HEAD SCREWS AND (4) METRIC M6x1x15MM SCREWS ARE PROVIDED FOR FASTENING TO RACKS.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- USE 110 STYLE TERMINATION TOOL FOR PUNCH DOWN.
- RETENTION CAPS (ONE PER CONNECTOR) PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.

PART NUMBER

NK5EPPG24Y

TITLE

NETKEY CAT5E 24 PORT PATCH PANEL

CUSTOMER DRAWING

ITEM REVISION NAME

M02479JN/00

DATASET FILE NAME


M02479JN_DC250/00B

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE: IN [mm]

.X ±
.XX ± .03 [.8]

.XXX ± .010 [.3]

ANGLES ±



THIRD ANGLE
PROJECTION

MATERIAL:

SEE NOTE 1

DRAWING NUMBER:

02479-250

DRAWN BY

DATE

CHK

SCALE

LZ

3-04-06

CEF

.25-1

SHT 1 OF 1

SIZE

A

REV	DATE	BY	CHK	APR	DESCRIPTION	ECN
1	5-13-14	MDJR	REFR	JCK	A. UPDATED TITLE BLOCK.	02479-250
R	3-04-06	LZ	CEF	CEF	RELEASED TO PRODUCTION	02479-250