



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
NK6PP48P	1.62 LB/10 PCS (733.9 g/EACH PC)



NOTES:


- SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
- SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- DIMENSIONS IN PARENTHESES ARE IN METRIC.
- THE PATCH PANEL IS DESIGNED FOR MOUNTING TO 19" UNIVERSAL RACKS.
- USE 110 STYLE TERMINATION TOOL FOR PUNCH DOWN.
- PART INCLUDES:
 - 1-PATCH PANEL ASSEMBLY
 - 8-LABEL COVERS
 - 8-LABELS
 - 1-SCREW KIT (INCLUDES FOUR (4) #12-24 SCREWS)
 - 1-SCREW KIT (INCLUDES FOUR (4) M6 SCREWS)
 - 48-RETENTION CAPS
- RETENTION CAPS ARE PROVIDED FOR SNAP-IN ON TERMINATED CONNECTORS.
- LABELS ARE PRE-NUMBERED (1-48) WITH BLANK SIDE FOR CUSTOM LABELING.

MODEL FILENAME	10M163AE/00	SIZE A
DRAWING FILENAME	10M163AE_DC02/00A	

NETKEY 48 PORT ALL MOLDED CATEGORY 6 PUNCHDOWN PATCH PANEL CUSTOMER DRAWING



I.I. NUMBER	N/A
PRODUCT SPEC/ PKG SPEC	N/A
ASSY METHOD/ TEST METHOD	N/A
SCALE	NONE



ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
 DIMENSIONAL TOLERANCES ARE:
 (.X) ± (.XXX) ± .010(.3)
 (.XX) ±.03(.8) ANGLES ±

DRAWN BY BJN	REVIEW DRAWING NUMBERS	PART NO. NK6PP48P
DATE 12-29-10	MAT'L BASE- REINFORCED PBT COVER- ABS	DRAWING NO. 10M163AE-02

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
R	12-29-10	BJN		RELEASED TO PRODUCTION	10M163AE-02				