


2

1



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT P/N	WEIGHT
MS8S2G	.54 LB/EACH PC (243.7 g/EACH PC)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN [] ARE IN METRIC.
4. PART INCLUDES:
1- 1X8 PASSIVE SATELLITE SPLITTER MODULE
1- GROUNDING SCREW



PART NUMBER		MS8S2G	
TITLE			
MEDIA DISTRIBUTION 1X8 PASSIVE SATELLITE VIDEO SPLITTER			
CUSTOMER DRAWING			
ITEM REVISION NAME		M03105AE/00	
DATASET FILE NAME		M03105AE_DC05/00B	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT MATERIAL: BRACKET - 16 GAGE C.R.S. VIDEO SPLITTER - ZINC PLATED STEEL	
.X ± .xx ± .03 [.8]			
.xxx ± .010 [.3] ANGLES ±		DRAWING NUMBER: 03105-05	
		THIRD ANGLE PROJECTION	
DRAWN BY	DATE	CHK	SCALE
JSP	10-15-08	REFR	NONE
SHT 1 OF 1			SIZE A

2

1