

2



1

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
UICFPSE4**	.70 LB/10 PCS (318.0 g/10 PCS)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
3. DIMENSIONS IN PARENTHESES ARE IN METRIC.
4. PART INCLUDES:
 - 1- FACEPLATE
 - 1- CLEAR SCREW COVER
 - 1- COLOR COORDINATED SCREW COVER
 - 2- CLEAR LABEL COVER
 - 2- MOUNTING SCREW



PART NUMBER		UICFPSE4**	
TITLE			
MINI-COM ULTIMATE ID 4 POSITION VERTICAL SLOPED EXECUTIVE SERIES FACEPLATE			
CUSTOMER DRAWING			
ITEM REVISION NAME		M01288BB/06	
DATASET FILE NAME		M01288BB_DC/06A	
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]		PANDUIT MATERIAL: ABS	
.X ± .XXX ± .010 [.3] .XX ± .03 [.8] ANGLES ±			
THIRD ANGLE PROJECTION		DRAWING NUMBER: 01288-07	
DRAWN BY	DATE	CHK	SCALE
JSP	7-24-02	JAJP	NONE
SHT 1 OF 1			SIZE A

1	5-14-14	BJN	JSP	MMR	REVISED & REDRAWN PREVIOUS REVISIONS REMVD FOR CLARITY	01288-07	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	

2

1