


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

ITEM NO.	PART NUMBER	DESCRIPTION	QTY.
1	Single Phase	Single Phase Monitor Display	1
2	Commando Plug	30Amp, 2P + E, Male	1
3	Cable - 3 Meters	3 Meter Length	1
4	Carling 20 Amp Double Pole	20Amp Double Pole MCB	2
5	C13	C13 10Amp IEC	14
6	C19	16 Amp IEC	2
7	BUTAL-01 Rev A	Mounting Button	2

DEFAULT OUTLETS STATE FOR CONTROLLABLE PDU	ON
INTERNAL POWER SUPPLY	NO
COMMUNICATION MODE	RS485



TITLE				30Amp, Single Phase, Vertical, PDU, 30Amp 3pin commando plug 3m Standard Cable, 30 amp split into two 15Amp branches with 20Amp Airpax Double Pole MCB, 7xC13 no individual neon, 1xC19 no individual neon (total per strip 14XC13XC19 2xMCB) Monitor only.	
CUSTOMER DRAWING					
ITEM REVISION NAME				13A095EM/00	
DATASET FILE NAME				13A095EM_DC02/00A	
				PART NUMBER:	
				V3X1D2A2N16AY	
				REF NUMBER:	
				OOB18	
DRAWN BY	DATE	CHK	SCALE	SIZE	
MDJR	6/05/14	JPMC	N/A	SHT 1 OF 1	
				A	

R	6/05/14	MDJR	JPMC	TSB	RELEASED TO PRODUCTION	13A095EM-02
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN