


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:


- **1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. CONSTRUCTED WITH CAT6A SCREENED 9 WIRE, FOUR SHIELDED TWISTED PAIR PLUS A 9TH WIRE, STRANDED 26AWG LSZH CABLE.
3. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUG AND 1-9TH POSITION CONTACT AT BOTH ENDS.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2011/65/EU ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.



PANDUIT PART NUMBER	MINIMUM CABLE LENGTH	WEIGHT
PVSTP6X1MB**	1 METER	68g/EACH
PVSTP6X2MB**	2 METERS	115g/EACH
PVSTP6X3MB**	3 METERS	156g/EACH
PVSTP6X5MB**	5 METERS	234g/EACH
PVSTP6X10MB**	10 METERS	433g/EACH

EIA/TIA T568B WIRING SCHEME	
PLUG POSITION	CABLE WIRE
1	ORANGE/WHITE
2	ORANGE
3	GREEN/WHITE
4	BLUE
5	BLUE/WHITE
6	GREEN
7	BROWN/WHITE
8	BROWN

PART NUMBER	PRODUCT SPEC/PKG SPEC
PVSTP6X*MB**	N/A
I.I. NUMBER	WORK INSTRUCTION
N/A	N/A

TITLE					
PANVIEW TX6A 10 GIG SHIELDED (LSZH) PATCH CORD					
CUSTOMER DRAWING					
ITEM REVISION NAME					
M02489AC/00					
DATASET FILE NAME					
M02489AC_DC03/00D					
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					
 THIRD ANGLE PROJECTION					
MATERIAL:					
DRAWING NUMBER:					
02489-03					
DRAWN BY	DATE	CHK	SCALE	SIZE	
MLJ	10-03-06	DKK	NONE	SHT 1 OF 1	A

3	1-31-04	BJN	MAT0	EJH	UPDATED	02489-03
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN