





THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PANDUIT PART NO.	WEIGHT
PEHF4	7.3 LBS. [3.3 Kg]

NOTES:

1. VISIT OUR ON-LINE CATALOG AT
WWW.PANDUIT.COM FOR A LIST OF
CURRENT PARTS APPLICABLE FOR USE
WITH THIS PRODUCT.
2. DIMENSIONS IN PARENTHESES ARE METRIC (mm).
3. PARTS SUPPLIED:
 - 1- PEHF CARRIAGE ASSEMBLY
 - 1- PEHF DOOR ASSEMBLY
 - 1- PACK OF 4 SCREWS
 - 1- INSTRUCTION SHEET



06A	11-26-13	BAME	FGR	CMK	UPDATED VIEWS	10V134AC-DC
05B	6-10-13	BAME	FGR	CMK	REVISED AND REDRAWN; PREVIOUS REVS OMITTED REVISED TITLE BLOCK	10V134AC-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN

TITLE		(PEHF4) PATCHRUNNER HIGH CAPACITY HORIZONTAL CABLE MANAGER			
		CUSTOMER DRAWING			
ITEM REVISION NAME		10V134AC/06			
DATASET FILE NAME		10V134AC_DC/06A			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]				MATERIAL:	
.X ± .XX ±				.XXX ± ANGLES ± N/A	
				DRAWING NUMBER:	
THIRD ANGLE PROJECTION				10V134AC-DC	
DRAWN BY	DATE	CHK	SCALE	SIZE	
PM	1-17-11	SRK	NONE	SHT 1 OF 1	
				A	