



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT P/N	WEIGHT
PEVF10	34.3 LBS/EACH (15.6 kg/EACH)

#### NOTES:

- VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
- COMPONENTS: (1) 10" SINGLE-SIDE VERTICAL MANAGER  
(1) HARDWARE KIT  
(1) FINGER KIT  
(2) DOOR BRACKETS  
(2) DOOR BRACKET BASES
- CAN BE USED WITH ANY 19 OR 23 INCH EIA STANDARD RACK.
- 3 ROWS OF 4RU 19" CEA OPENINGS (12 TOTAL RU'S).
- 10" DOOR SOLD SEPARATELY (P/N: PED10).
- DIMENSIONS IN PARENTHESIS ARE METRIC.
- ALL DIMENSIONS ARE REFERENCE ONLY.

TITLE PATCHRUNNER HIGH CAPACITY VERTICAL MANAGER 10" WIDE, SINGLE-SIDED (PEVF10) CONTROL DRAWING				
ITEM REVISION NAME 09V054AF/07			<b>PANDUIT</b>	
DATASET FILE NAME 09V054AF_DC/07A				
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN (mm)			MATERIAL:  BACKBONE- STEEL FINGERS- ABS	
			DRAWING NUMBER: 09V054AF - DC	
DRAWN BY BAME	DATE 2/3/10	CHK NAGL	SCALE NONE	SIZE A
SHT 1 OF 1				

07A	5/1/14	BAME	FGR	CMK	PREVIOUS REVISIONS OMITTED DOOR BRACKETS REVISED	09V054AF-DC
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN