


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO.	WEIGHT
PZC12S	90 LBS/EACH 40.8 kg/EACH

NOTES:

- VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A LIST OF CURRENT PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
- DIMENSIONS IN PARENTHESES ARE METRIC (mm).
- CAN BE USED WITH ANY 19" EIA STANDARD COMPONENT UP TO 17.5" DEEP IN ADDITION TO ALL PANDUIT HORIZONTAL CABLE MANGEMENT AND PATCH PANEL PRODUCTS.
- 12 AVAILBLE RACK SPACES PLUS 2 BONUS RACK SPACES (TOP & BOTTOM) FOR SHALLOW EQUIPMENT SUCH AS POWER STRIPS, MODEMS, ETC.
- VERTICAL EQUIPMENT MOUNTING ANGLES ARE ADJUSTABLE FRONT TO REAR OF CABINET ON 1" INCREMENTS.
- LOAD CAPACITY, 250-LBS.
- INSTALLS IN EITHER A HINGED RIGHT OR HINGED LEFT APPLICATION.
- FRONT ACCESS THROUGH DOOR; REAR ACCESS THROUGH HINGED MID-SECTION.
- MATERIAL: STEEL- POWDER COATED BLACK

							TITLE PANZONE 12RU HINGED WALL MOUNT CABINET (PZC12S) SOLID DOOR CUSTOMER DRAWING					
							ITEM REVISION NAME V10290ZZ/04.PRT				<div>PANDUIT</div>	
							DATASET FILE NAME V10290ZZ.DC/04A.PRT					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .03 [0.8] .xxx ± .007 [.18] .xx ± .018 [.46] ANGLES ± 1 °					
							<div><div></div><div></div></div> THIRD ANGLE PROJECTION					
04A	12-4-13	LDR	BAME	CMK	REVISED REV SCHEME	10290-58						
00A	10-16-04	MAV			RELEASED TO PRODUCTION	10290-58	MATERIAL: SEE NOTES					
							DRAWING NUMBER: 10290-58					
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY LDR	DATE 12-4-13	CHK	SCALE NONE	SHT 1 OF 1	SIZE A