


1. IDENTIFICATION: VERTICAL, (24) 5-20R
NETWORKED & ENVIRONMENTAL MONITORED
120V / 30A / THREE-PHASE WYE POU

PANDUIT P/N	WEIGHT
QN1A1P3BN24E1	17 lb (7.7 kg)

<u>PART NO.</u>	<u>COLOR</u>
QN1A1P3BN24E1	BLACK


2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS
3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. POWER (A,V,PF,KWH) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION, LOCAL DISPLAY, OR OPTIONAL REMOTE DISPLAY (PVQ-RD).
5. UL® & c-UL® LISTED 60950.
6. RoHS COMPLIANT.
7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.
8. MAXIMUM AVAILABLE INPUT POWER = 8.6 KW
9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




DETAIL A
(SCALE 4X)


TOOLLESS MOUNTING
BUTTON 2X




TOOLLESS MOUNTING BUTTON LOCATION



20 AMP, 2 POLE UL LISTED ELECTRO
MECHANICAL SWITCH/BREAKER
3 PLACES



PLUG
30 AMP, 120/208V x 3~ WYE
TWIST LOCK
NEMA L21-30P



TWENTY-FOUR (24)
RECEPTACLES
20 AMP, 125V
STRAIGHT BLADE
NEMA 5-20R

01A	8-29-12	PIP	MRWA	A. UPDATED DETAIL A. B. ADDED BUTTON MOUNTING NOTE.		09V098JV				
00A	11-22-11	MRWA	KRKE	RELEASED TO PRODUCTION		09V098JV				
REV	DATE	BY	CHK	DESCRIPTION		ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098JV/01.PRT	
CAD FILENAME/LAYERS		09V098JV_DC/01A.PRT	
 PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, (24) 5-20R NETWORKED & ENVIRONMENTAL MONITORED POWER OUTLET UNIT CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: INCHES X.X +/- 0.03 X.XX +/- 0.015 X.XXX +/- 0.005		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION	
[METRIC - MILLIMETER] X +/- 0.8 X.X +/- 0.4 X.XX +/- 0.13		ANGLE +/- 1°	
DRAWN BY MRWA		SCALE NONE	
DATE 11-22-11		DRAWING NO. 09V098JV	
CHK'D KRKE		DWG 	