

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT P/N	WEIGHT
QN1B1P3BN30P1	17 lb (7.7 kg)

NOTES:

1. IDENTIFICATION: VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED & ENVIRONMENTAL MONITORED 208V / 30A / THREE-PHASE WYE POU

PART NO. COLOR  
QN1B1P3BN30P1 BLACK

2. ACCESSORY COMPONENTS:  
(4) #10-32 x 1/2" MOUNTING SCREWS  
(4) #12-24 x 1/2" MOUNTING SCREWS  
(2) #10-32 LOCKING COLLAR SCREWS  
(2) L-BRACKETS

3. DIMENSIONS IN PARENTHESES ARE METRIC (mm).

4. POWER (A,V,PF,KWH) MONITORING AND ENVIRONMENTAL SENSOR DATA CAN BE ACCESSED REMOTELY VIA ETHERNET CONNECTION, LOCAL DISPLAY, OR OPTIONAL REMOTE DISPLAY (PVQ-RD).


5. UL® & c-UL® LISTED 60950.

6. RoHS COMPLIANT.

7. VISIT OUR ON-LINE CATALOG AT WWW.PANDUIT.COM FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.


8. MAXIMUM AVAILABLE INPUT POWER = 8.6 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.




DETAIL A  
(SCALE 4X)


TOOLLESS MOUNTING  
BUTTON 2X



TOOLLESS MOUNTING BUTTON LOCATION





NETWORKED ETHERNET CONNECTION  
(SEE DETAIL A)




20 AMP, 2 POLE UL LISTED ELECTRO  
MECHANICAL SWITCH/BREAKER  
3 PLACES

10 FOOT INLET POWER CORD

 PLUG  
30 AMP, 120/208V x 3~ WYE  
TWIST LOCK  
NEMA L21-30P

 TWENTY-FOUR (24)  
RECEPTACLES  
15 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13

 SIX (6)  
RECEPTACLES  
20 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C19

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
01A	8-29-12	PIP	MRWA	A. UPDATED DETAIL A. B. ADDED BUTTON MOUNTING NOTE.	09V098KF				
00A	11-22-11	MRWA	KRKE	RELEASED TO PRODUCTION	09V098KF				

MODEL FILENAME	09V098KF/01.PRT	
CAD FILENAME/LAYERS	09V098KF_DC/01A.PRT	
<b>PANDUIT</b> CORP TINLEY PARK, ILLINOIS		
VERTICAL, MIXED (24) C-13 & (6) C-19 NETWORKED & ENVIRONMENTAL MONITORED POWER OUTLET UNIT CUSTOMER DRAWING		
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
INCHES	X.X +/- 0.03	[METRIC - MILLIMETER] X.X +/- 0.8
	X.XX +/- 0.015	X.XX +/- 0.4
	X.XXX +/- 0.005	X.XX +/- 0.13
ANGLE	+/- 1°	
DRAWN BY	MRWA	MAT'L:
DATE	11-22-11	
CHK'D	KRKE	
SCALE	NONE	
DRAWING NO.	09V098KF	DWG SIZE
		B