




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



NOTES:

1. [] DENOTE MILLIMETERS
2. TEMPERATURE RANGE:
-40°F (-40°C) TO 120°F (60°C)
3. RoHS COMPLIANT



										CAD FILENAME/LAYERS				111084BD_DC_C10956/08B				
										PANDUIT CORP. TINLEY PARK, ILLINOIS								
										PSL-USBB USB TYPE "B" BLOCKOUT CUSTOMER DRAWING								
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .05 (.XX) ± .03						UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.		
										DRAWN BY JHAC						SCALE 4 : 1		
										DATE 03/13/12						DRAWING NO. C10956		DWG A
										CHK'D								SIZE
			</															