


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




PART NO.	MATERIAL	PKG. QTY.
MMP350H-C	304 S.S.	100
MMP350H-C316	316 S.S.	100
MMP350H-M	304 S.S.	1000
MMP350H-M316	316 S.S.	1000

NOTES:

- BRACKETS [] DENOTES DIMENSIONS ARE IN MILLIMETERS
- CUSTOM PERMANENT MARKING AVAILABLE. CONSULT FACTORY.
- USE WITH HEAVY CROSS SECTION MLT'S
- TOLERANCE (UNLESS OTHERWISE SPECIFIED)
 $.xxx = \pm .020 (.51)$
 $.xx = \pm .03 (.8)$

SECTION "A-A"

							TITLE					
09A	3/13	JAMB	MIM	RGRO	UPDATED DRAWING TO NEW PANDUIT GLOBAL TITLE BLOCKWITH PANDUIT LOGO. ADDED DIM 0.37 & 2.38	SSECN01031	METAL MARKER PLATE – HEAVY					
08B	8/08	JAMB	SKB	---	ADDED PART NO’S FOR BULK QTY 1000 MARKER PLATES	-----	CUSTOMER DRAWING					
08A	7/07	JAMB	SKB	---	REMOVED PART NO'S MMP350W38–C & MMP350W38–C316 FROM PART TABLE . REMOVED FIGURE 2 & SECTION "B–B"	-----	ITEM REVISION NAME		N41046BS/09			
07	1/07	JAMB	SKB	---	ADDED MAT'L THICKNESS DIM TO SECTION "A–A" & "B–B"	-----	DATASET FILE NAME		N41046BS_DC/09A			
06	11/06	JAMB	SKB	---	REVISED FIGURE 1 HEAVY MARKER PLT & ADDED FIGURE 2 STD MARKER PLT USED WITHSTD MLT CROSS SECTION	SS00287	UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm]					MATERIAL:
05	10/03	BRH	DPN	JB	ADDED PACKAGE QTY/CODE TO PART NUMBERS IN TABLE	11167	.x ± .1 [2.54] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °					STAINLESS STEEL
04	02/01	KMD	JAC	JAC	FILE SPEC WAS N41046SA_PCD_03	09066	 THIRD ANGLE PROJECTION				DRAWING NUMBER:	
											N41046BS_DC	
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							SAM	2/4/91	JAC	1:1		A