




THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	PACKAGE QUANTITY	MAX BUNDLE DIA [mm]	LENGTH "L" +/- .8 [mm]
MS4W75T30-Q2	25	4" [102]	20.2" [513]
MS6W75T30-Q2	25	6" [152]	26.5" [673]
MS8W75T30-Q2	25	8" [203]	32.7" [831]
MS10W75T30-Q2	25	10" [254]	39.0" [991]



NOTES:

1. APPLICATION TOOLS: BT75SDT
2. BRACKETS [] DENOTES DIMENSIONS ARE IN MILLIMETERS AND ARE FOR REFERENCE ONLY
3. MATERIAL: 201 STAINLESS STEEL

							TITLE DISCRETE LENGTH STRAPPING .750" [19.05mm] WIDE CUSTOMER DRAWING					
							ITEM REVISION NAME N41283BS/02					
							DATASET FILE NAME N41283BS_DC/02A					
							UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: IN [mm] .x ± .1 [.254] .xxx ± .005 [.127] .xx ± .01 [.25] ANGLES ± 5 °  THIRD ANGLE PROJECTION					
02A	4/13	JAMB	MIM	RGR0	UPDATE DRAWING TO NEW GLOBAL PANDUIT TITLE BLOCK WITH PANDUIT LOGO. ADDED TO NOTE 2: "AND ARE FOR REFERENCE ONLY	SSECN01057	MATERIAL: SEE NOTES					
01A	6/10	MIM	CCH	---	BUCKLE GEOMETRY REVISED	-----	DRAWING NUMBER: N41283BS_DC					
00A	5/09	MIM	CCH	---	DRAWING RELEASED	-----						
REV	DATE	BY	CHK	APR	DESCRIPTION	ECN	DRAWN BY	DATE	CHK	SCALE	SHT 1 OF 1	SIZE
							MIM	5/09	SKB	NONE		A