




NOMINAL DUCT SIZE (W)	C in (mm)	TC in (mm)	HC in (mm)
.5	.69 (17.5)	.040 (1.0)	.230 (5.8)
.75	.94 (23.8)	.050 (1.3)	.240 (6.1)
1	1.25 (31.8)	.060 (1.5)	.350 (8.9)
1.5	1.75 (44.5)	"	"
2	2.25 (57.2)	"	"
2.5	2.75 (69.9)	"	"
3	3.25 (82.6)	.065 (1.6)	.370 (9.4)
4	4.25 (108.0)	"	"
6	6.25 (158.8)	.080 (2.0)	"

1. SEE CURRENT CATALOG FOR ADDITIONAL PART NUMBER
SUFFIXES TO INDICATE COLOR AND OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESIS ARE METRIC.

PART NO. SYSTEM
COVER EXAMPLE
C 1.5 LG 6
TYPE — WIDTH — COLOR — LENGTH (ft)

										CAD FILENAME/LAYERS				D34518BA_PVC_COVER_02A			
										PANDUIT CORP. TINLEY PARK, ILLINOIS							
										WIRING DUCT COVER FOR DUCT TYPES "S", "D", "E", "F", "FS", AND "G" CUSTOMER DRAWING							
																	
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) : (.XXX) : (.XX) : ANGLES :				UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.			
2	8-24-01	JCST	JKG	D. CHANGED TOLERANCE C. MADE "C" A REFERENCE DIMENSION		34518-17	JKG	JKG			DRAWN BY DW		MAT'L: POLYVINYL CHLORIDE		SCALE NONE		
1	2/11/00	JHNU	HIW	B. .18 WAS .125/ 4.5 WAS 3.2 A. REV'D TITLE: ADDED FS AND G DUCT TYPE		34518-17	HIW	HIW			DATE 10-29-93				DRAWING NO.		
R	10-29-93	DW	CEF	RELEASED TO PRODUCTION.		34518-17	CEF				CHK'D CEF				34518-17		
REV	DATE	BY	CHK	DESCRIPTION		ECN	R	CUST	SUP		CEF				A SIZE		