THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NUMBER	DESCRIPTION
FIASXN-9612-10S	QUICKNET HDQ HIGH DENSITY CASSETTE OM3 STANDARD FIBER STRAIGHT THROUGH
FIASXN-9612-10F	QUICKNET HDQ HIGH DENSITY CASSETTE OM3 STANDARD FIBER FLIPPED
FIASXO-9612-10S	QUICKNET HDQ HIGH DENSITY CASSETTE OM3 OPTIMIZED FIBER STRAIGHT THROUGH
FIASXO-9612-10F	QUICKNET HDQ HIGH DENSITY CASSETTE OM3 OPTIMIZED FIBER FLIPPED
FIASZN-9612-10S	QUICKNET HDQ HIGH DENSITY CASSETTE OM4 STANDARD FIBER STRAIGHT THROUGH
FIASZN-9612-10F	QUICKNET HDQ HIGH DENSITY CASSETTE OM4 STANDARD FIBER FLIPPED
FIASZO-9612-10S	QUICKNET HDQ HIGH DENSITY CASSETTE OM4 OPTIMIZED FIBER STRAIGHT THROUGH
FIASZO-9612-10F	QUICKNET HDQ HIGH DENSITY CASSETTE OM4 OPTIMIZED FIBER FLIPPED

NOTES:
1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
   a. CASSETTE MATERIAL: ALUMINUM & STEEL
   b. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE WEIGHT: 40.8oz [1157.7g]
5. DIMENSIONS IN BRACKETS ARE METRIC



REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH
R	10/21/09	MTV		RELEASED TO PRODUCTION	F00118AD-DC			

QUICKNET HDQ SERIES HIGH DENSITY CASSETTE
1RU 96 FIBER ANGLED 12 FIBER MTP TO LC
CUSTOMER DRAWING

PANDUIT™ CORP.
TINLEY PARK, ILL 60477

THIRD ANGLE PROJECTION

ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.
DIMENSIONAL TOLERANCES ARE:
(.X) (.XXX)±.010 [0.3]
(.XX)±.03 [0.8] ANGLES

DRAWN BY: MTV
DATE: 10-21-09
CHK'D:
REVIEW DRAWING NUMBERS:

DRAWING FILENAME: F00118AD_DC/01A
SCALE: 1:4
PART NO.: SEE TABLE
DRAWING NO.: F00118AD-DC
SIZE: A