



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

DUPLEX LC TO LC FIBER OPTIC PATCH CORD							
PANDUIT PART NO.	CABLE				LC CONNECTOR		
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR
F5PE10-10M*	PLENUM (OFNP)	50/125um OM2	DUPLEX 1.6mm ZIPCORD	ORANGE	0.25dB	20dB	BLACK
F6PE10-10M*		62.5/125um OM1					ELECTRIC IVORY
FXPE10-10M*		10GbE OM3		AQUA	0.25dB	26dB	AQUA
FXOPE10-10M*		OPTIMIZED 10GbE OM3			0.15dB	26dB	
FZPE10-10M*		10GbE OM4		AQUA	0.25dB	26dB	AQUA
FZOPE10-10M*		OPTIMIZED 10GbE OM4			0.15dB	26dB	
F9PE10-10M*		9/125um OS1		YELLOW	0.35dB	55dB	BLUE

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

										FIBER OPTIC PATCH CORD DUPLEX LC TO LC CONFIGURATION CUSTOMER DRAWING					
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477					
										 THIRD ANGLE PROJECTION		ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) ±.03 (.XXX) ±.010 (.3) ±.008 ANGLES		DRAWING FILENAME M02779BC_DC/01A	
										DRAWN BY MC		REVIEW DRAWING NUMBERS		PART NO. SEE SHEETS 2, 3 & 4	
										DATE 04-27-07		DRAWING NO. 02779-11		SIZE A	
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-11						CHK'D	RAF	SHEET 3 OF 4		
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH						

