

MTP TO MTP FIBER OPTIC PATCH CORD													
PANDUIT PART NO.	CABLE				MTP CONNECTOR								
	RATING	FIBER TYPE	COUNT	COLOR	MAX. IL	MIN. RL	BOOT COLOR						
F64D5-5M*Y	PLENUM (OFNP)	62.5/125um	4	ORANGE	0.50dB	20dB	BLACK						
F66D5-5M*Y			6										
F68D5-5M*Y			8										
F612D5-5M*Y			12										
F512D5-5M*Y		50/125um	12	ORANGE	0.50dB	20dB							
FX12D5-5M*Y		10GbE OM3	12	AQUA	0.50dB	26dB							
FX012D5-5M*Y		OPTIMIZED 10GbE OM3			0.35dB	26dB							
FZ12D5-5M*Y		10GbE OM4	12	AQUA	0.50dB	26dB							
FZ12D5-5F*					0.35dB	26dB							
FZ012D5-5M*		OPTIMIZED 10GbE OM4											
FZ012D5-5F*													
F94D5-5M*Y		9/125um OS1	4	YELLOW	0.75dB	55dB	BLACK						
F96D5-5M*Y			6										
F98D5-5M*Y			8										
F912D5-5M*Y			12										

* - DENOTES PATCH CORD LENGTH, WHERE M = METERS AND F = FEET

								FIBER OPTIC PATCH CORD MTP TO MTP CONFIGURATION CUSTOMER DRAWING				
								 PANDUIT TM CORP. TINLEY PARK, ILL 60477				
								ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (X) ±.03 (XXX) ±.010 (0.3) ANGLES THIRD ANGLE PROJECTION				
								DRAWING FILENAME M02779BG_DC/01A				
								SCALE NONE				
								PART NO. SEE SHEETS 2 & 3				
01	09-09-09	EFK		RELEASED TO PRODUCTION	02779-15					DATE 05-03-07	DRAWING NO. 02779-15 SHEET 2 OF 3	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D RAF	SIZE A	

