



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



FRONT VIEW

SHOWN W/O DUSTCAPS




PORT DESIGNATIONS

AS VIEWED FROM THE FRONT
WITH THE ADAPTERS REMOVED FOR CLARITY

PANDUIT P/N	DESCRIPTION
FCXO-12-10Y	OPTIMIZED 50/125 10GbE MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FCX-12-10Y	50/125 10GbE MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FCZO-12-10Y	OPTIMIZED 50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FCZ-12-10Y	50/125 10GbE OM4 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FC6-12-10Y	62.5/125 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FC5-12-10Y	50/125 MULTIMODE 12 FIBER, MTP TO LC CASSETTE MODULE
FC9-12-10Y	9/125 SINGLEMODE 12 FIBER, MTP TO LC CASSETTE MODULE

NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
A. MODULE HOUSING AND COVER: PLASTIC
B. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 3.82oz (108.2g)
5. DIMENSIONS IN BRACKETS ARE METRIC.



										FIBER OPTIC CASSETTE MODULE 12 FIBER MTP TO DUPLEX LC CONFIGURATION CUSTOMER DRAWING			
										 PANDUIT TM CORP. TINLEY PARK, ILL 60477			
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (0.3) (.XX) ±.03 (0.8) ANGLES			
										DRAWING FILENAME M02068AL_DC/00E			
										SCALE NONE			
										PART NO. SEE TABLE			
										DRAWING NO. 02068-45			
										SIZE A			
02	09-17-09	EFK		RELEASED TO PRODUCTION	02068-45								
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH				