



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.




FRONT VIEW
SHOWN W/O DUSTCAPS


PANDUIT P/N	DESCRIPTION
FCZ-24-10BY	50/125 10GbE OM4 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE
FCZO-24-10BY	OPTIMIZED 50/125 10GbE OM4 MULTIMODE 24 FIBER, MTP TO LC CASSETTE MODULE


NOTES:

1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITIES.
2. SEE CATALOG FOR COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PRODUCT.
3. MATERIALS:
A. BOX AND LID: POWDER COATED ALUMINUM
B. ADAPTER: COMPOSITE PLASTIC
4. CASSETTE MODULE WEIGHT: 7.25oz (205.6g)
5. DIMENSIONS IN BRACKETS ARE METRIC.



PORT DESIGNATIONS
AS VIEWED FROM
THE FRONT
ADAPTERS REMOVED FOR CLARITY



										FIBER OPTIC CASSETTE MODULE FLIPPED 24 FIBER, LC TO MTP CONFIGURATION CUSTOMER DRAWING			
										 PANDUIT™ CORP. TINLEY PARK, ILL 60477			
										ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± .010 (0.3) (.XX) ± .03 (0.8) ANGLES		DRAWING FILENAME MO2068AV_DC/00A	
										THIRD ANGLE PROJECTION		SCALE NONE	
										DRAWN BY EFK		REVIEW DRAWING NUMBERS	
										DATE 09-16-09		PART NO. SEE TABLE	
										CHK'D		DRAWING NO. 02068-64	
												SIZE A	
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH				
R	09-16-09	EFK		RELEASED TO PRODUCTION	02068-64								