


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PART NUMBER	DESCRIPTION	COLOR	MAXIMUM LOSS
FODPX06Y FODRX06Y	MULTIMODE 50/125um 10GbE OM3	AQUA	3.5dB/KM @ 850nm 1.5dB/KM @ 1300nm
FODPZ06Y FODRZ06Y	MULTIMODE 50/125um 10GbE OM4		3.5dB/KM @ 850nm 1.5dB/KM @ 1300nm





PLENUM - FODPX06Y/FODPZ06Y			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
440 N (100 lbf)	110 N (25 lbf)	96 mm (3.8 in)	48 mm (1.9 in)
TEMPERATURE			
INSTALLATION	OPERATION	STORAGE	
0°C TO +50°C 32°F TO +122°F	0°C TO +50°C 32°F TO +122°F	-40°C TO +65°C -40°F TO +149°F	
RISER RATED - FODRX06Y/FODRZ06Y			
TENSILE LOAD		BEND RADIUS	
INSTALLATION	LONG TERM	INSTALLATION	LONG TERM
660 N (150 lbf)	165 N (37 lbf)	96 mm (3.8 in)	48 mm (1.9 in)
TEMPERATURE			
INSTALLATION	OPERATION	STORAGE	
0°C TO +50°C 32°F TO +122°F	0°C TO +50°C 32°F TO +122°F	-40°C TO +65°C -40°F TO +149°F	

NOTES:

1. DIAMETER DIMENSION, SHOWN FOR REFERENCE ONLY.
2. CABLE SUPPLIED IN 2500 METER (8202 FT) LENGTHS.
3. FOR PART NUMBERS AND LENGTHS OTHER THAN THOSE SHOWN, CONTACT YOUR PANDUIT SALES PERSON.
4. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.

WEIGHT OF 2.5km REEL/BOX	
OFNP	OFNR
78.0 kg (172 lbs)	73.5 kg (162 lbs)

										MULTIMODE 50/125um OPTI-CORE 10GbE OM3 & OM4 6 FIBER DISTRIBUTION CABLE WITH 900um TIGHT BUFFER CUSTOMER DRAWING		
										 PANDUIT ™ CORP. TINLEY PARK, ILL 60477		
										 THIRD ANGLE PROJECTION ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED. DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ± 0.3 (.010) (.XX) ± 0.8 (.03) ANGLES		
										DRAWING FILENAME M02055BE_DC_06-10G/01A		
										SCALE NONE		
										PART NO. FODP*06Y FODR*06Y		
										DRAWING NO. 02055-29		
										SIZE A		
02	10-21-09	EFK		RELEASED TO PRODUCTION	02055-29						DATE 08-25-04	CHK'D WMA
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH			