


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
FR24X4**10 (SEE NOTE 1)	120.00 IN ±.18 IN (3048.0mm ±4.6mm)	54.80 LB (24857g)	5.48 LB/FT (82g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D39701BT_DC/00 FR24X4

CAD_FILENAME/LAYERS

FR24X4 . pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
FIBERRUNNER 24x4 CHANNEL
(FR24X4**10)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

$$\begin{array}{l} (.X) \pm \\ (.XX) \pm .03 \end{array} \quad \begin{array}{l} (.XXX) \pm \\ \text{ANGLES} \pm \end{array}$$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY

MSO

DATE	10-21-08
------	----------

CHK'D	SL
-------	----

MAT'L:	
--------	--

PVC

SCALE	NONE
-------	------

DRAWING NO.
39701 - 15

DWG
A
SIZE

R	10-21-08	MSO	SL	RELEASED TO PRODUCTION	39701-15	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH