


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NO.	DIMENSIONS					WEIGHT
	A (REF)	B (REF)	C	D	E (REF)	lbs / 100pcs (kg) / 100pcs
BR-1.25-14WS	1.18 [30]	2.91 [74]	0.32 [8] MINIMUM	0.217 [5.5] 0.201 [5.1]	1.00 [25]	6.3 (2.9)
BR-2.0-14WS	2.00 [51]	3.73 [95]	0.32 [8] MINIMUM	0.217 [5.5] 0.201 [5.1]	1.00 [25]	9.3 (4.2)



ISOMETRIC VIEW

NOTES:

1. SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.

DIMENSIONS IN BRACKETS ARE METRIC [mm]			
CAD FILENAME/LAYERS G03668BL_DC_GB3668BL/02A			
		CORP. TINLEY PARK, ILLINOIS	
BR - - 14WS WOOD SCREW BRIDLE RING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ±0.05 [1.3] (.XXX) ±0.010 [0.25] (.XX) ±0.02 [0.5] ANGLES ±5°		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
DRAWN BY ARHA	MAT'L: LOW CARBON STEEL BRIGHT ZINC ELECTROPLATE	SCALE NONE	
DATE 09-15-09 CHK'D <i>KCN</i>		DRAWING NO. G03668BL	DWG A SIZE

O2A	09/15/09	ARHA	<i>ARH</i>	INITIAL RELEASE	GB3668BL	O2A	<i>KW</i>			
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP		