


PANDUIT PART NUMBER	LENGTH	WEIGHT	WEIGHT/LENGTH
HC2**2 (SEE NOTE 1)	78.74 IN $\pm$.18 IN (2000.0mm $\pm$ 4.6mm)	0.79 LB (358g)	0.12 LB/FT (1.8g/cm)
HC2**6 (SEE NOTE 1)	72.00 IN $\pm$.18 IN (1828.8mm $\pm$ 4.6mm)	0.72 LB (327g)	0.12 LB/FT (1.8g/cm)

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. DIMENSIONS IN PARENTHESES ARE IN METRIC.



ENG. REF.: D38258CH_DC_HC2_00.prt

CAD FILENAME/LAYERS

HC2.pdf

PANDUIT CORP TINLEY PARK, ILLINOIS
FIBERRUNNER 2x2 HINGED COVER
(HC2**2, HC2**6)
CUSTOMER DRAWING

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:

(.X) $\pm$ (.XXX) $\pm$
(.XX) $\pm$.03 (0.8) ANGLES $\pm$

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN IN
INCHES, THIRD ANGLE PROJECTION.

DRAWN BY
MSO

DATE
1-8-07

CHK'D
RN

MAT'L:

PVC

SCALE
NONE

DRAWING NO.
38258-23

DWG
A
SIZE

R	1-8-07	MSO	RN	RELEASED TO PRODUCTION	38258-23	RN	RN		
REV	DATE	BY	CHK	DESCRIPTION	ECN	- R	CUST	SUP	GMBH