



Material	High Conductivity Seamless Copper Tube
Plating	Electro-Tin
Wire Size	250 STR/FLEX
Wire Type	Stranded Copper: Class G, H, I, K, M, Locomotive
Wire Strip Length	1-1/16 in.
Stud Size	1/4 in.
UL Listed Wire Connector	Yes, for applications up to 35kv. Consult cable manufacturer for voltage stress relief instructions with applications greater than 2000 volts.
UL Temperature Rating	90° C
C.S.A Certified Wire Connector	Yes
Panduit Color Code on Barrel	YELLOW
Panduit Die Index No. on Barrel	P62
Alternate Industry Die Index No. () on Barrel	(16)



						 PANDUIT CORP. TINLEY PARK, ILLINOIS	
						LCAX250-14-X Copper Lug - One-Hole, Standard Flex Barrel	
00	1/08	JHNU	LEM	RELEASED		SCALE N/A DRAWING NO / CAD FILE LCAX250-14-CUST	
REV	DATE	BY	CHK	DESCRIPTION	ECN		