


Diagram illustrating the dimensions and components of a standard 19-inch rack:

- Overall Length:** L
- Overall Width:** W
- Hole Spacing:** S
- Hole Diameter:** .53 DIA THRU-HOLE TYP. [13.5]
- Insulation Mounting Holes:** Indicated by arrows pointing to the top and bottom rows of holes.



REV	DATE	BY	CHK	REV	DESCRIPTION	ECN	PM	CUST	CHK'D	DATE	DRAWN BY	MAT'L	SCALE	NONE	DWG	DRAWING NO / CAD FILE	DWG	B	SIZE
03	11/08				JHNUJHNU	REVISED DRAWING LAYOUT. REMOVED BRACKET VIEWS													
02	11/08				JHNUJDWA	ADDED MOUNTING HARDWARE COLUMN TO TABLE													
01	7/08				JHNUJDWA	ADDED HOLE PATTERN COLUMN TO TABLE													
00	5/08				JHNUJDWA	DRAWING RELEASED													
REV	DATE	BY	CHK	REV	DESCRIPTION	ECN	PM	CUST	CHK'D	DATE	DRAWN BY	MAT'L	SCALE	NONE	DWG	DRAWING NO / CAD FILE	DWG	B	SIZE

PANDUIT PART NUMBER	DIMENSIONS - IN [mm]			HOLE PATTERN INFORMATION			MOUNTING BRACKET HARDWARE	MOUNTING KIT QUANTITY
	L	W	S	HOLE SIZE	HOLE SPACING	# OF HOLE SETS		
GB4N0007TPI-1	12.00 [304.8]	4.00 [101.6]	1.25	1/2"	1.75	7 SETS	BUTTON HEAD SCREW	2
GB4N0016TPI-1	24.00 [609.6]	4.00 [101.6]	1.25	1/2"	1.75	16 SETS	BUTTON HEAD SCREW	2
GB4N0024TPI-1	36.00 [914.4]	4.00 [101.6]	1.25/1.38	1/2" 1/2"	1.75	14 SETS 10 SETS	BUTTON HEAD SCREW	2
GB4N0026TPI-1	48.00 [1219.2]	4.00 [101.6]	1.56	1/2"	1.75	26 SETS	HEX BOLT	3
GB4N0034TPI-1	60.00 [1524.0]	4.00 [101.6]	1.56	1/2"	1.75	34 SETS	HEX BOLT	3