




NOTES:


1. SEE CURRENT CATALOG FOR PART NUMBER SUFFIXES TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
2. MATERIAL:
OUTER HOUSING: PLASTIC
BOOTS: THERMOPLASTIC RUBBER
FERRULE: ZIRCONIA CERAMIC
HARDWARE: BRASS
3. FULLY COMPLIES WITH THE FIBER OPTIC CONNECTOR PERFORMANCE REQUIREMENTS AS SPECIFIED BY TIA/EIA-568-B.3.
4. COMPATIBLE WITH TIA-EIA-604-3 (FOCIS-3)
5. ALL MATERIALS AND COMPONENTS USED MUST MEET THE MATERIAL RESTRICTIONS OF RoHS, (EUROPEAN DIRECTIVE 2002/95/EC ON THE RESTRICTION OF HAZARDOUS SUBSTANCES) AS PROPOSED BY THE RoHS TECHNICAL ADAPTATION COMMITTEE.
6. DIMENSIONS IN BRACKETS ARE METRIC [mm]




PANDUIT PART NUMBER	APPLICATION	BOOT COLOR	WEIGHT
NKFSCMWH	62.5/125 OM1	WHITE	.090 lb/10 pcs [40.8g/10 pcs]
NKFSCMBL	50/125 OM2	BLACK	
NKFSCMAO	50/125 OM3	AQUA	
NKFSCSWH	9/125 OS1/OS2	WHITE	



SC CONNECTOR WITH 3mm BOOT
(SHOWN WITHOUT DUST CAP)



SC CONNECTOR WITH 900um BOOT
(SHOWN WITHOUT DUST CAP)

										NETKEY FIBER OPTIC SINGLEMODE/MULTIMODE SIMPLEX SC CONNECTOR CUSTOMER DRAWING				
											 PANDUITTM CORP. TINLEY PARK, ILL 60477			
										 THIRD ANGLE PROJECTION	ALL DIMENSIONS ARE GIVEN IN INCHES UNLESS OTHERWISE SPECIFIED.		DRAWING FILENAME M01302AB_DC/00A	
											DIMENSIONAL TOLERANCES ARE: (.X) (.XXX) ±.010 (.03) (.XX) ±.03 (.08) ANGLES		SCALE NONE	
										DRAWN BY EFK	MATERIAL		PART NO. NKFSCM** NKFSCS**	
R	12-21-09	EFK		RELEASED TO PRODUCTION	01302-67					DATE 12-21-09			DRAWING NO. 01302-67	SIZE A
REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH	CHK'D				