

PANDUIT P/N	WEIGHT
QZ1C1P3BN1851	17 lb (7.7 kg)

DETAIL A  
(SCALE 4X)

(SCALE 4X)

1.750  
(44.4)

0.750  
(19.0)

31.500  
(800.1)

TOOLLESS MOUNTING BUTTON LOCATION

REAR VIEW

$$\begin{array}{r} 33.000 \\ - (838.2) \end{array}$$

20 AMP, 2 POLE UL LISTED ELECTRO  
MECHANICAL SWITCH/BREAKER  
(3 PLACES)

NETWORKED CURRENT METER  
(SEE DETAIL A)

– 10 FOOT INLET POWER CORD      FRONT VIEW

1. IDENTIFICATION: 33" VERTICAL, MIXED (9) C-13 & (3) C-19 & (6) 5-20R  
NETWORKED  
208V / 30A / THREE-PHASE WYE POU  
PART NO. COLOR  
QZ1C1P3BN1851 BLACK

(4) #10-32 x 1/2" MOUNTING SCREWS  
(4) #12-24 x 1/2" MOUNTING SCREWS  
(2) #10-32 LOCKING COLLAR SCREWS  
(2) L-BRACKETS

4. CURRENT METER - RED, 4-DIGIT LED DISPLAY PROVIDES TRUE RMS CURRENT THAT CONTINUOUSLY SCROLLS THROUGH THE THREE DIFFERENT MEASURED CIRCUITS. METER DISPLAYS CIRCUIT NAME FOLLOWED BY THE MEASURED CURRENT (E.G. CR-1 REPRESENTS PHASE 1). BREAKER/AGGREGATE CURRENT MONITORING CAN ALSO BE ACCESSED REMOTELY VIA ETHERNET CONNECTION.

6. RoHS COMPLIANT.

7. VISIT OUR ON-LINE CATALOG AT [WWW.PANDUIT.COM](http://WWW.PANDUIT.COM) FOR A CURRENT LIST OF PRODUCTS APPLICABLE FOR USE WITH THIS PART.

8. MAXIMUM AVAILABLE INPUT POWER = 8.65 KW

9. INSTALLATION SHALL COMPLY WITH ALL APPLICABLE NATIONAL, STATE, AND LOCAL CODES.

Figure 1 shows a square specimen with dimensions 3.440 (87.4) and 3.500 (88.9). The specimen has four circular features: two small circles on the left and two larger circles on the right, one of which is shaded.

RIGHT SIDE VIEW

PLUG  
30 AMP, 120/208V x 3~ WYE  
TWIST LOCK  
NEMA L21-30P

SIX (6)  
RECEPTACLES  
20 AMP, 125V  
STRAIGHT BLADE  
NEMA 5-20R

NINE (9)  
RECEPTACLES  
15 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C13

THREE (3)  
RECEPTACLES  
20 AMP, 250V  
STRAIGHT BLADE  
IEC 60320/C19

00A	11-16-11	MRWA	KRKE	RELEASED TO PRODUCTION	09V098HO				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098HO/00.PRT	
CAD FILENAME/LAYERS		09V098HO_DC/00A.PRT	
<div>PANDUITCORP</div> <div>TINLEY PARK, ILLINOIS</div>			
33" VERTICAL, MIXED (9) C-13 & (3) C-19 & (6) 5-20R NETWORKED POWER OUTLET UNIT (QZ1C1P3BN1851) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES		ALL DIMENSIONS ARE GIVEN IN	
X.X +/- 0.03		INCHES, THIRD ANGLE PROJECTION	
X.XX +/- 0.015			
X.XXX +/- 0.005			
[METRIC - MILLIMETER]			
X. +/- 0.8			
X.X +/- 0.4			
X.XX +/- 0.13			
ANGLE			
+/- 1°			
DRAWN BY		SCALE	
MRWA		NONE	
DATE		DRAWING NO.	
11-16-11		09V098HO	
CHK'D		DWG	
KRKE		B	
		SIZE	