


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE lbs. (N)	CROSS * SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLTIM-60	.06 (1.5)	.87 (22)	.043 (1.1)	.098 (2.5)	.170 (4.3)	.154 (3.9)	.188 (4.8)	3.9 (99)	18 (80)	M	CURVED	.07 (32)
PLT2S-60	.06 (1.5)	1.88 (48)	.052 (1.3)	.190 (4.8)	.260 (6.6)	.220 (5.6)	.320 (8.1)	7.4 (188)	50 (222)	S	CURVED	.29 (132)

NOTES :

- * 1) SEE www.panduit.com FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE AND PART COLOR.
* 2) CABLE TIE CROSS-SECTION CODE: M=MINIATURE, I=INTERMEDIATE, S=STANDARD & H=HEAVY.
3) MATERIAL HAS A UL RELATIVE THERMAL INDEX RATING OF 248°F (120°C).
4) MATERIAL FLAMMABILITY RATING: UL94V-0.
5) MINIMUM LOOP TENSILE RATING AT 120°F (49°C)/20% RH.
6) COLOR: BLACK

W10001EF/01-SS-26944_05.PRT

										CADD FILENAME/LAYERS		DIMENSIONS IN PARENTHESIS ARE IN METRIC UNITS	
										PANDUIT CORP. TINLEY PARK, ILLINOIS			
										PAN-TY CABLE TIES BLACK FLAME RETARDANT -60 SERIES			
										UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± .--- (.XXX) ± .020(.51) (.XX) ± .02(.5) ANGLES ± .---		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
---	----	---	---	REVISED NOTE 1 "SEE CURRENT PRICE SHEET..." TO "SEE www.panduit.com ..."		----	---	---					
5	11/15/11	JABO	TGS	CORRECTED BUNDLE DIA MAX, & 'C' DIM OF PLT2S		SS-26944	5	TGS		DRAWN BY KET	MAT'L: BLACK		SCALE NONE
4	8/9/11	JABO	TGS	CORRECTED 'F' DIMENSION OF PLTIM-60		SS-26944	4	TGS		DATE 2-3-95	FLAME RETARDANT NYLON 6.6		DRAWING NO. SS-26944
REV	DATE	BY	CHK	DESCRIPTION		ECN	R	CUST	SUP	CHK'D HVP			DWG SIZE A