


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



PANDUIT PART NO. *	BUNDLE DIA.		A in (mm)	B in (mm)	C in (mm)	D in (mm)	E in (mm)	F in (mm)	MIN. LOOP TENSILE ** lbs. (N)	CROSS SECTION	TIP STYLE	WEIGHT lbs./100 pcs. (g)
	MIN. in (mm)	MAX. in (mm)										
PLT1M-71	.06 (1.5)	.87 (22)	.048 (1.2)	.101 (2.6)	.192 (4.9)	.130 (3.3)	.190 (4.8)	4.00 (101.6)	35 (156)	MINIATURE	CURVED	.08 (36)
PLT1.5M-71	.06 (1.5)	1.38 (35)	.048 (1.2)	.101 (2.6)	.192 (4.9)	.130 (3.3)	.190 (4.8)	5.90 (149.9)	35 (156)	MINIATURE	CURVED	.11 (52)
PLT2S-71	.13 (3.3)	1.88 (48)	.055 (1.4)	.190 (4.8)	.260 (6.6)	.240 (6.1)	.320 (8.1)	7.40 (188)	150 (668)	STANDARD	STRAIGHT	.38 (173)

NOTES:

- *1) SEE CURRENT PRICE SHEET FOR PART NUMBER SUFFIX DESIGNATION FOR PACKAGE SIZE.
- 2) MATERIAL HAS A UL RELATIVE THERMAL INDEX RATING OF 500°F (260°C).
- 3) MATERIAL FLAMMABILITY RATING: UL94V-0.
- 4) EXCELLENT RESISTANCE TO MOST CHEMICALS.
- **5) MINIMUM LOOP TENSILE RATING AT 73°F (23°C).

WI0035DS/03 SS_27424.PRT

DIMENSIONS IN PARENTHESES ARE IN METRIC UNITS

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP
6	10/11/10	BWG	MPH	UPDATED 1M AND 1.5M DIMENSIONS B, D, E AND F.	27424	6		BOBK

PANDUIT CORP. TINLEY PARK, ILLINOIS

PAN-TY CABLE TIES
PLT ELEVATED TEMPERATURE SERIES

UNLESS OTHERWISE SPECIFIED,
DIMENSIONAL TOLERANCES ARE:
(.X) ± .1(2.5) | (.XXX) ± .020(.51)
(.XX) ± .02(5) | ANGLES ± -----

UNLESS OTHERWISE SPECIFIED,
ALL DIMENSIONS ARE GIVEN
IN INCHES, THIRD ANGLE PROJECTION.

DRAWN BY: JABO
DATE: 06/01/04
CHK'D: DM

MAT'L: PEEK
COLOR: BROWN
REG. T.M. OF VICTREX MFG. LTD.

SCALE: NONE

DRAWING NO.: SS-27424
DWG SIZE: A