


THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

NOTES:

- \*\* 1. SEE CURRENT CATALOG FOR VARIOUS APPLICATIONS AND TO INDICATE COLOR AND/OR PACKAGE QUANTITY.
- △ B 2. SEE CATALOG FOR A COMPLETE LIST OF PARTS APPLICABLE FOR USE WITH THIS PART.
- 3. TERMINATED WITH (8 POSITION) SHIELDED MODULAR PLUGS ON BOTH ENDS PER T568A.
- △ J 4. CONSTRUCTED WITH 26AWG STRANDED CAT5e F/UTP LSZH/CM PATCH CABLE. CABLE COLOR: INTERNATIONAL GRAY
- 5. MATERIAL:  
 PLUG: POLYCARBONATE  
 SHIELD: COPPER ALLOY NICKEL PLATED  
 BOOT: THERMOPLASTIC RESIN  
 CABLE: DUAL-RATED CM/LSZH
- △ I  
 △ K 6. NOMINAL CABLE JACKET DIAMETER IS 0.205 IN (5.21MM).



△ F T568A WIRING SCHEME

PLUG POSITION:	CABLE WIRE:
1	WHITE/GREEN
2	GREEN
3	WHITE/ORANGE
4	BLUE
5	WHITE/BLUE
6	ORANGE
7	WHITE/BROWN
8	BROWN

SEE SHEET 2 FOR PATCH CORD LENGTHS AND PART NUMBERS

MODEL FILENAME	SIZE
DRAWING FILENAME	A
M01895CB_DC07/00E	

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
4	5-13-10	BJN		N. ADDED IDENTIFICATION LABEL M. ADDED TANGLE-FREE LATCH K. ADDED NEW NOTE 6 L. ADDED BROWN	01895-07				
3	3-4-10	BJN	KA	J. SPECIFIED LSZH/CM PATCH CABLE: NOTE 4	01895-07		PBD		
2	5-9-08	BJN	EJH	I. ADDED CABLE SPEC; MOVED BOOT COLORS TO SH2	01895-07		REGA		
1	4-23-07	BJN	EJH	G. TX5e WAS CAT 5E H. ADDED SHIELD F. ADDED T568A WIRING SCHEME E. MOVED CABLE P/N TO SH2 C. ADDED COLOR TABLE D. ADDED MODULAR A. ADDED SH2 B. ADDED NOTE 2	01895-07		REGA		
R	6-4-06	BJN	EJH	RELEASED TO PRODUCTION	01895-07	EJH	REGA		

△ G TX5e SHIELDED PATCH CORDS (CM/LSZH)  
CUSTOMER DRAWING

<p>PANDUIT™ CORP. TINLEY PARK, ILL 60477</p>	I.I. NUMBER
	PRODUCT SPEC/ PKG SPEC
<p>THIRD ANGLE PROJECTION</p>	ASSY METHOD/ TEST METHOD
	SCALE
<p>ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED.</p> <p>DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010 (.XX) ± ANGLE ±</p>	PART NO.
<p>DRAWN BY: BJN</p> <p>DATE: 6-4-06</p> <p>CHK'D: EJH</p>	<p>STPCHAAMB**</p> <p>DRAWING NO. 01895-07 SHEET 1 OF 2</p>

THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.



TX5e SHIELDED PATCH CORDS

PART NUMBER	LENGTH(MIN) ft(m)
STPCH0.5MB**	1.64ft (0.5m)
STPCH1MB**	3.28ft (1m)
STPCH1.5MB**	4.92ft (1.5m)
STPCH2MB**	6.56ft (2m)
STPCH2.5MB**	8.20ft (2.5m)
STPCH3MB**	9.84ft (3m)
STPCH4MB**	13.12ft (4m)
STPCH5MB**	16.40ft (5m)
STPCH6MB**	19.68ft (6m)
STPCH7MB**	22.97ft (7m)
STPCH8MB**	26.25ft (8m)
STPCH9MB**	29.53ft (9m)
STPCH10MB**	32.80ft (10m)
STPCH15MB**	49.21ft (15m)
STPCH20MB**	65.62ft (20m)
STPCH25MB**	82.02ft (25m)
STPCH30MB**	98.42ft (30m)
STPCH35MB**	114.83ft (35m)
STPCH40MB**	131.23ft (40m)



BOOT COLORS	** = COLOR
BLACK	BL
BLUE	BU
RED	RD
YELLOW	YL
GREEN	GR
BROWN	BR



MODEL FILENAME		SIZE
DRAWING FILENAME		A
M01895CB_DC07/00E		
TX5e SHIELDED PATCH CORDS (CM/LSZH) CUSTOMER DRAWING		
 <b>PANDUIT</b> ™ CORP. TINLEY PARK, ILL 60477		I.I. NUMBER
		PRODUCT SPEC/ PKG SPEC
 ALL DIMENSIONS ARE GIVEN IN INCHES, UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE: (.X) ± (.XXX) ± .010 (.XX) ± ANGLE ±		ASSY METHOD/ TEST METHOD
DRAWN BY BJN		SCALE NONE
DATE 6-4-06		PART NO. STPCHAAMB**
CHK'D EJH		DRAWING NO. 01895-07 SHEET 2 OF 2

REV	DATE	BY	CHK	DESCRIPTION	ECN	R	CUST	SUP	OTH
4	5-13-10	BJN		SEE SHEET 1 FOR REVISIONS	01895-07				
3	3-4-10	BJN	KAA	SEE SHEET 1 FOR REVISIONS	01895-07		PBD		
2	5-9-08	BJN	EJH	SEE SHEET 1 FOR REVISIONS	01895-07		REGA		
1	4-23-07	BJN	EJH	SEE SHEET 1 FOR REVISIONS	01895-07		REGA		