



- NOTES:
- 1. PART NUMBERS: RGEJ660U, RGEJ696U, RGEJ1024URT
 - 2. DIMENSIONS IN INCHES, DIMENSIONS IN BRACKETS ARE MILLIMETERS



RGEJ660U, RGEJ696U

FACTORY CRIMPED #6 AWG/16mm SQ. JUMPER WIRE ASSEMBLY (QTY. 1) INCLUDES:
LCC6-14JAW (QTY. 1)
LCC6-10ABW (QTY. 1)
#6 AWG/16mm SQ. WIRE - GREEN/YELLOW INSULATION

PANDUIT PART NUMBER	L IN [mm]
RGEJ660U	60.00 [1524.0]
RGEJ696U	96.00 [2438.4]
RGEJ1024URT	24.00 [609.6]



RGEJ1024URT

FACTORY CRIMPED #10 AWG/6mm SQ. JUMPER WIRE ASSEMBLY (QTY. 1) INCLUDES:
PV10-10RX (QTY. 2)
#10 AWG/6mm SQ. WIRE - GREEN/YELLOW INSULATION

									10J021BB-JC/00A
									PANDUIT CORP. TINLEY PARK, ILLINOIS
									STRUCTURED GROUND EQUIPMENT GROUNDING JUMPERS (RGEJ660U, RGEJ696U, RGEJ1024URT) CUSTOMER DRAWING
									UNLESS OTHERWISE SPECIFIED DIMENSIONAL TOLERANCES ARE: (.X) ± --- (.XXX) ± --- (.XX) ± --- ANGLES ± ---
									UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION
								DRAWN BY JHNU	MAT'L:
								DATE 2/11	SCALE NONE
00	2/11	JHNU	JHNU	DRAWING RELEASED	10J021BB-JC	FLD	FLD	SEE NOTES	DRAWING NO / CAD FILE 10J021BB-JC
REV	DATE	BY	CHK	DESCRIPTION	ECN	-R	SUP	CHK'D	DWG B SIZE