



NOTES:
1. IDENTIFICATION: VERTICAL, (12) L6-20R,
208V / 30A / SINGLE-PHASE POU

2. ACCESSORY COMPONENTS:
 (4) #10-32 x 1/2" MOUNTING SCREWS
 (4) #12-24 x 1/2" MOUNTING SCREWS
 (2) #10-32 LOCKING COLLAR SCREWS
 (2) L-BRACKETS

7. MAXIMUM AVAILABLE POWER = 5 KW

PANDUIT P/N	WEIGHT
VB0B1L2BN12J1	17 lb (7.7 kg)



PLUG
30 AMP, 250V, SINGLE-PHASE
TWIST LOCK
NEMA L6-30P



TWELVE (12)
RECEPTACLES
20 AMP, 250V
TWIST LOCK
NEMA L6-20R

00A	2-24-11	MAV	KRRE	RELEASED TO PRODUCTION	09V098DV				
REV	DATE	BY	CHK	DESCRIPTION	ECN - R	CUST	SUP	OTH	

MODEL FILENAME		09V098DV/00.PRT	
CAD FILENAME/LAYERS		09V098DV_DC/00A.PRT	
PANDUIT CORP TINLEY PARK, ILLINOIS			
VERTICAL, (12) L6-20R, POWER OUTLET UNIT (VB0B1L2BN12J1) CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED,	
INCHES		ALL DIMENSIONS ARE GIVEN IN	
X.X +/- 0.03		INCHES, THIRD ANGLE PROJECTION	
X.XX +/- 0.015			
X.XXX +/- 0.005			
[METRIC - MILLIMETER]			
X. +/- 0.8			
X.X +/- 0.4			
X.XX +/- 0.13			
ANGLE			
+/- 1°			
DRAWN BY		SCALE	
MAV		NONE	
DATE		DRAWING NO.	
2-24-11		09V098DV	
CHK'D		DWG	
KRKE		B	
		SIZE	