



THIS COPY IS PROVIDED ON A RESTRICTED BASIS AND IS NOT TO BE USED IN ANY WAY DETRIMENTAL TO THE INTERESTS OF PANDUIT CORP.

PANDUIT PART NUMBER	WEIGHT
WG18**10	21.5 LB/EACH 9752.3 g/EACH

NOTES:

1. SEE CURRENT CATALOG FOR ADDITIONAL PART SUFFIXES TO INDICATE PART FINISH AND/OR PACKAGING QUANTITY.
2. DIMENSIONS IN PARENTHESIS ARE METRIC.



CAD FILENAME/LAYERS		09D017D0_DC/00B WG18**10	
PANDUIT		CORP. TINLEY PARK, ILLINOIS	
WYR-GRID CABLE TRAY 18" WIDE		STRAIGHT SECTION 10' LONG (WG18**10)	
CUSTOMER DRAWING			
UNLESS OTHERWISE SPECIFIED, DIMENSIONAL TOLERANCES ARE:		UNLESS OTHERWISE SPECIFIED, ALL DIMENSIONS ARE GIVEN IN INCHES, THIRD ANGLE PROJECTION.	
(.X) ± .125 (3.18) ANGLES ± (.XX) ± .125 (3.18) ANGLES ±		(.XXX) ± (.XXX) ±	
DRAWN BY JAHA		MAT'L:	
DATE 5-3-10		SEE NOTES ABOVE	
CHK'D SL		SCALE NONE	
		DRAWING NO. 09D017D0-DC	
		DWG SIZE A	

REV	DATE	BY	CHK	DESCRIPTION	ECN	CHK	CUST	SUP
I	5-17-10	JAHA	SL	B. REVISED PART NAME A. REVISED TOLERANCE	09D017D0-DC	RN	RN	
R	5-3-10	JAHA	SL	RELEASED TO PRODUCTION	09D017D0-DC	RN	RN	