


QUADCAB® Wall Mount Cabinets

Contents: 1 rear section (arrives disassembled facilitating installation)
1 front door
2 19" mounting angles

1 center section with 2 CH751 locks
2 top/bottom cover plates
2 hinge pins
2 security cotter pins

Rack Units	Height	Width	Depth	Door Style	Color*	RWU**	Catalog No.
12	24" (610)	22.6" (574)	20" (508)	Window	Black	2	HSQ24
12	24" (610)	22.6" (574)	26" (660)	Window	Black	2	HSQ2426
12	24" (610)	22.6" (574)	36" (914)	Window	Black	2	HSQ2436
12	24" (610)	22.6" (574)	20" (508)	Solid	Black	2	HSQ24S
12	24" (610)	22.6" (574)	26" (660)	Solid	Black	2	HSQ24S26
12	24" (610)	22.6" (574)	36" (914)	Solid	Black	2	HSQ24S36
19	36" (914)	22.6" (574)	20" (508)	Window	Black	4	HSQ36
19	36" (914)	22.6" (574)	26" (660)	Window	Black	4	HSQ3626
19	36" (914)	22.6" (574)	36" (914)	Window	Black	4	HSQ3636
19	36" (914)	22.6" (574)	20" (508)	Solid	Black	4	HSQ36S
19	36" (914)	22.6" (574)	26" (660)	Solid	Black	4	HSQ36S26
19	36" (914)	22.6" (574)	36" (914)	Solid	Black	4	HSQ36S36
26	48" (1219)	22.6" (574)	20" (508)	Window	Black	6	HSQ48
26	48" (1219)	22.6" (574)	26" (660)	Window	Black	6	HSQ4826
26	48" (1219)	22.6" (574)	36" (914)	Window	Black	6	HSQ4836
26	48" (1219)	22.6" (574)	20" (508)	Solid	Black	6	HSQ48S
26	48" (1219)	22.6" (574)	26" (660)	Solid	Black	6	HSQ48S26
26	48" (1219)	22.6" (574)	36" (914)	Solid	Black	6	HSQ48S36

Note: *For Office White, add "W" to the end of the Catalog No.

**RWU = Rear Wall Unit.



HSQ48



HSQ36

Equipment Shelf, Cantilevered

For use with all QUADCAB® enclosures

Contents: 1 shelf and mounting hardware kit



Description	Dimensions	Color	Catalog. No.
Solid	3.5"H x 17"W x 14"D	Black	MCCCS19
Perforated	3.5"H x 17"W x 14"D	Black	MCCCS19P

Equipment Shelf, Stationary

For use with 36" deep QUADCAB® enclosures

Contents: 1 shelf and mounting hardware kit



Description	Dimensions	Color	Catalog. No.
Solid	17.7" W x 29.2" D	Black	CKSSD
Perforated	17.7" W x 29.13" D	Black	MCCPSHLF

Fan Kit

Increases ventilation.

Contents: 1 fan tray assembly, (2 fans - 57 CFM each) wired and mounting hardware kit



Description	Catalog No.
114 CFM, 120 VAC, 60 Hz, 36 dBA	HWKF120
114 CFM, 230 VAC, 50 Hz, 36 dBA	HWKF230

Fan Plate/Fan

Increases ventilation

Contents: 1 fan, 1 wire guard, 4 lock nuts, screws, and washers and 1 cord with 6' plug



Description	Catalog No.
Blank plate with 4" fan/PVC conduit knock-out	H1KB
Fan, 57 CFM, 120V AC, 60 Hz, 36 dBA	REKEF