



Modular Plugs

Specifications

Snap On Plug

- UL Listed
- 50 micro-inch gold-plated
- For solid cable

Modular Plugs

- UL Listed File
- 50 micro-inch gold-plated
- UL 94-V0 rated

Snap On Modular Plug

Description	Insulated Conductor Range	Catalog No.
Snap on, 8-position modular plug	.032-.038	BRFTP4P

Modular Plugs

Description	Category	Insulated Conductor Range	AWG	Catalog No.
8-position/8-contact, snagless	5e	.032-.038	24-26	BRMOD4PSN25



BRFTP4P



BRMOD4PSN25

Continuity Tester

Features/Benefits

- Compact size
- One button test results

Specifications

- Tests up to 320 feet
- Built-in BNC connector with F-connector

UOM: main and remote continuity test units, 2 F-connector adapters, 2 RJ45 shielded patch cables, 2 belt clips

Description	Catalog No.
Continuity Tester	TCT2



TCT2

Crimp Tool

Features/Benefits

- Color-coded die-sets for different plug sizes
- Ratchet cycle assures no-fault crimps

Specifications

- Parallel compression terminates to FCC specs — no misalignment

Description	Catalog No.
Complete tool kit in durable plastic case includes: crimp tool, 3 die-sets, UTP cable stripper. Die-sets include: RJ45, RJ22 and RJ11	UCTKIT
Crimp tool frame (die-sets sold separately)	UCT
RJ11 die-set	CTDSR11
RJ22 die-set	CTDSR22
RJ45 die-set (snagless or non-snagless)	CTDSR45
RJ45 die-set (non-snagless only)	CTDSR45S
RG6 and RG59 hex crimp die-set	CTDSRG659
Economy crimp tool – includes non-replaceable RJ11, RJ22 and RJ45 die-sets	ECT
RG6 and RG59 compression tool	COMPTRG659



UCT



CTDSR11



CTDSR22



CTDSR45



ECT